

APPLICATION INSTRUCTIONS

Tattoo SBB Maxima

Tattoo SBB Maxima is designed for dyed polyester textiles. Low transfer temperatures coupled with an exclusive barrier layer are extremely effective in preventing the migration of dyes.

FEATURES:



**PU
water-
based**



120µ



**Cotton, polyester,
blended fabrics..**
Less suitable for nylon
and other coated textiles.



**EcoSolvent (incl. TrueVis),
Solvent, Latex, UV**

CUTTING CONDITIONS:



**Blade
30 - 45°**



**low/
medium**



30 - 40 cm/s

TRANSFER CONDITIONS:



135°C



10 s



**medium/
high**



Cold peel



60°C



1. Print and cut



2. Weed design



3. Apply tape



4. Transfer, remove tape,
done !

Printing profiles at www.seftextile.com

Recommended transfer tape: FlexTape; connected designs can also be transferred without tape.

Drying time: Depending on ink and conditions 1 - 6h

For small designs, it can be useful to first apply the tape over the whole surface and then to weed it from the back.

Store in a cool and dry place; protect against the influence of light when stored. We recommend not to exceed a storage period of 12 months. The technical specifications rest on extensive tests and technical research. Due to the variety of possible influences during refinement, and use, the specifications should be viewed as reference values. We recommend a suitability test on the original material. A legally binding warranty of specific characteristics cannot be derived from our specifications.

► PACKAGING

